

## ER-AS

### ER-AS for air extraction from WCs.

- with AFR 80 aluminium flexible duct for duct network made of folded spiral-seams duct or
- with MF-F90 flexible duct without transition piece or
- with 90° MF-B75 steel elbow or MF-FSM75 connector on MF-F75 flexible duct

Extraction socket for Maico ER-UPD and ER-UP/G for WC seat air extraction. Air extraction of room and WC seat at the same time.

Pre-requirement: The flushing pipe from the recessed-mounted toilet cistern is fitted with a DN 70 branch.


Connection from flushing pipe to the HT DN 70 fan, resulting in reduced air speeds and effective, draught-free extraction.

Combination with ER 60 or ER 100.

Cistern recommendation: Manufacturer TECE, TECEprofil Universal module for WC with TECE cistern with connection for odour extraction. TECE Order no.: 9,300,003

[www.tece.de](http://www.tece.de)

Phone: +49 (0) 25 72 / 928-0



- ① ER-UP ... recessed-mounted housing
- ② ER-AS extraction socket
- ③ Connection to exhaust air duct network:
- ④ DN 70 HT duct